



DCG414T2

54V XR FLEXVOLT 125mm Angle Grinder Kit (2 x Batteries)

Selling Proposition

- 54V Brushless motor enables improved performance in demanding applications
- Electronic Brake stops the wheel quickly when the trigger is disengaged
- Electronic clutch reduces the kickback reaction in the event of a pinch or stall
- A mesh cover over air intake vents restricts dust being sucked through the motor
- Rubber overmold provides enhanced grip and comfort
- Recessed spindle lock design allows max depth of cut and greater protection to button when using in confined spaces

Standard Equipment

- 2 position side handle
- Keyless protective guard
- Blade Wrench
- Multi-voltage charger
- 2 x 54V XR Flexvolt Li-Ion battery packs with state of charge indicator

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Input	
No Load Speed	9000 rpm
Max. Disc Diameter	125 mm
Spindle Thread	M14
Weight	2.9 kg
Length	400 mm
Height	125 mm
Hand/Arm Vibration - Grinding	5.9 m/s ²