

Oil drain plugs




- **Material**
Glass-fibre reinforced polyamide based (PA) technopolymer. Resistant to solvents, oils, greases and other chemical agents.
- **Colour**
Red similar to RAL 3000, matte finish.
- **Packing ring**
NBR synthetic rubber.
- **Maximum continuous working temperature**
100°C.
- **Graphic symbol "drain"**
According to DIN regulations.

Technical data

The tightening torque indicated in the table guarantees an optimal tightness, keeping the packing ring in the correct position.

Accessories on request

TSD. oil fill plugs are suitable for mounting aluminium plates with graphic symbols type MH..



Code	Description	d	h	s	L	M	Tightening torque [Nm]	⚖️
59942	TSD.10x1.5	M10x1.5	9	19	16	15	4÷5	4
59944	TSD.12x1.5	M12x1.5	9	19	16	15	6÷8	4
59946	TSD.14x1.5	M14x1.5	9	19	16	15	6÷8	5
59948	TSD.16x1.5	M16x1.5	9	22	16	17	8÷10	7
59950	TSD.18x1.5	M18x1.5	11	26	18	20.5	8÷10	8
59952	TSD.20x1.5	M20x1.5	11	26	18	20.5	8÷10	8
59954	TSD.22x1.5	M22x1.5	12	32	20	25	10÷12	12
59956	TSD.25x1.5	M25x1.5	12	32	20	25	10÷12	12
59958	TSD.26x1.5	M26x1.5	12	32	20	25	10÷12	14
59960	TSD.35x1.5	M35x1.5	13	38	22	31	15÷18	15
59964	TSD.40x1.5	M40x1.5	14	46	24	38	15÷18	20
59972	TSD.1/8	G 1/8	9	19	16	15	4÷6	4
59974	TSD.1/4	G 1/4	9	19	16	15	4÷6	4
59976	TSD.3/8	G 3/8	9	22	16	17	8÷10	5
59978	TSD.1/2	G 1/2	11	26	18	20.5	8÷10	8
59980	TSD.3/4	G 3/4	12	32	20	25	10÷12	14
59982	TSD.1	G 1	13	38	22	31	15÷18	18
59986	TSD.1¼	G1 1/4	14	46	24	38	15÷18	20
59988	TSD.1½	G1 1/2	15	55	26	46	15÷18	24