

Technical data sheet

Article number:
924-00434

QDF5-6

Product Group	Quick Connect Female Funnel Entry
Product Family	Double Grip Pre-Insulated Terminals
Material	Brass (BS), Polyvinylchloride (PVC), Copper (CU)
Colour	Yellow (YE)

Application Range	Low Voltage
Conductor Size Range mm²	4.0-6.0 mm ²
Diameter (D)	7 mm
Length (L)	24 mm
Length (L2)	13.5 mm
Length (L3)	10.5 mm
Max Current	24 A
Max Voltage	300 V
Operating Temperature	+75 °C
Package Content	50 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	6.7 mm

