

JT.T – 3/8" Hex bit socket



Description:

- **HIGH PERFORMANCE** – Designed and manufactured for high tightening forces.
- **BIT PROFILE** – For female drive fasteners.
- **NECK-DOWN DESIGN** – Facilitating the use in narrow spaces.
- **Matte finish**
- **ISO 2725-1, DIN 3124**

| | Hex size (mm) | Square Drive | Diameter (mm) | Length (mm) | Weight (g) |
|--------|---------------|--------------|---------------|-------------|------------|
| JT.3T | 3 | 3/8" | 17.9 | 51 | 0.038 |
| JT.4T | 4 | 3/8" | 17.9 | 51 | 0.038 |
| JT.5T | 5 | 3/8" | 17.9 | 51 | 0.038 |
| JT.6T | 6 | 3/8" | 17.9 | 51 | 0.04 |
| JT.7T | 7 | 3/8" | 17.9 | 51 | 0.04 |
| JT.8T | 8 | 3/8" | 17.9 | 51 | 0.04 |
| JT.10T | 10 | 3/8" | 17.9 | 51 | 0.05 |