

Description

STAINLESS STEEL TOP PLATE CASTOR, POLYAMIDE 80MM

Fixed

KF41BA080-77L

Part Number

Swivel


KP41BA080-77L

Swivel and brake

KP41BD080-77L



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	80 mm		
Overall Height H	108 mm ±1		
Size of plate A X B	105 x 85 mm±1		
Plate hole centres a x b	80 x 60 mm±0,3		
Plate hole	9 mm		
Offset F ±1	\	36 mm	36 mm
Width of Tread	30 mm±0,5		
Hardness of tread	shore A ± 83°		
Load capacity	150 Kg		
Weight	0,4 kg	0,6 kg	0,74 kg
Temperature	- 20 / + 80 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
Fastening by top plate.
Total lock. Metal pedal.

Wheel :

Wheel of White Polyamide 6. Non marking.
Hub : Plain bore.

Features :

Low starting effort. High load capacity.
Lightweight, highly resistant to knocks and other impacts as well as a great many chemical substances.
Corrosion resistant, easy to clean. Specially designed for humid environments.
Suited for Food industry, Hospital or Industrial Kitchen equipment.
Non staining.
Medium duty.