

"PanelSeT SM compact enclosure with glazed door - 1800x800x400 mm"

Local distributor code:

383547167 NSYSM18840T

EAN Code: 3606485120973

Main

Range	PanelSeT	
product name	PanelSeT SM	
Product or component type	Compact enclosure	
Application	Multi-purpose	
Installation accessory type	Floor-standing	
Device composition	body cable gland plate locking system with handle: door mounting plate bracket door	
Removable parts	Door by screws hinge Mounting plate bracket by screws	
Enclosure nominal height	1800 mm	
Enclosure nominal width	800 mm	
Enclosure nominal depth	400 mm	

Complementary

Number of doors	Front: 1 door(s)	
Door opening side	Reversible (120 °)	
Door type	Glazed	
Lock type	4 points lock, handle with 5 mm double bar insert	
Body type	Single piece body with welded rear panel Front part forming a rigid frame with welded corners	
Mounting plate description	Without mounting plate	
Type of gland plate	Standard	
cable entry	1 entry	
Material	Door: Securit glass Body: sheet steel Door: sheet steel Hinge: zamak	
Surface finish	Epoxy-polyester powder	
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)	
Accessibility for operation	Front	
Product weight	94 kg	

Environment

Standards	IEC 62208
Product certifications	UL DNV BV
IK degree of protection	IK08 conforming to IEC 62262 conforming to UL conforming to cUL
IP degree of protection	IP55 conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	193.000 cm
Package 1 Width	85.000 cm
Package 1 Length	49.000 cm
Package 1 Weight	76.000 kg

Logistical informations

Country of origin

Contractual warranty

Coverage	Core product
Warranty	18 months

30 Jun 2025



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	668
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	52da316e-d4e1-4114-85c0-32a03b2934fd
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions




Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features



Product datasheet

NSYSM18840T

Technical Illustration

Exploded view



Image of product / Alternate images

Alternative











