

2400 RSC24/7-VIS

		art.
	024004037	2400 RSC24/7-VIS

- n. 21 **42:** combination wrenches
6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-24-27-30-32 mm
n. 9 **96BPC/SC9:** ball head offset hexagon key wrenches $\odot$
1,5-2-2,5-3-4-5-6-8-10 mm
n. 7 **96T:** offset hexagon key wrenches $\odot$ 2-2,5-3-4-5
6-8 mm
n. 1 **111E:** Adjustable wrench 250 mm
n. 2 **35:** flat chisels, ribbed type 100-200 mm
n. 1 **1052:** self - locking pliers 240 mm
n. 1 **1128BMX:** electrician's scissors, straight blades
n. 1 **1370:** engineer's hammer 300 g
n. 1 **1390:** soft face hammer $\varnothing$ 35 mm
n. 1 **1692/5:** measuring tape 5 m
n. 1 **1719BMA...Q:** second-cut square files 200 mm
n. 1 **1719BMA...T:** second-cut triangular files 200 mm
n. 1 **1719BMA...P:** second-cut flat files 200 mm
n. 1 **1719BMA...M:** second-cut half-round files 200 mm
n. 1 **1719BMA...R:** second-cut round files 200 mm
n. 1 **1771:** snap - off blade utility knife
n. 13 **900:** 1/4" hexagon sockets $\odot$ 4-4,5-5-5,5-6-7-8-9-10-11-12-13-14 mm
n. 6 **900ME:** 1/4" socket drivers for hexagon screws $\odot$ 2,5-3-4-5-6-8 mm
n. 1 **900/20:** 1/4" drive extension bar 50 mm
n. 1 **900/21:** 1/4" drive extension bar 150 mm
n. 1 **900/25:** 1/4" drive universal joint
n. 1 **900BG/30:** 1/4" drive spinner handle
n. 1 **900/42:** 1/4" drive swivel T-handle
n. 1 **900/55:** 1/4" reversible ratchet $\oplus$
n. 19 **920A:** 1/2" square drive hexagon sockets $\odot$
10-11-12-13-14-15-16-17-18-19-20
21-22-23-24-26-27-30-32 mm
n. 1 **920/25:** 1/2" drive universal joint
n. 1 **920AN/125:** 1/2" wobble extension bar 125 mm
n. 1 **920AN/250:** 1/2" wobble extension bar 250 mm
n. 1 **920/42:** 1/2" drive sliding T-handle
n. 1 **920/55:** 1/2" drive reversible ratchet $\oplus$
n. 1 **1032:** circlip pliers straight, internal $\odot$ 180 mm
n. 1 **1034:** circlip pliers bent, internal $\odot$ 170 mm
n. 1 **1036:** circlip pliers straight, external $\bullet$ 175 mm
n. 1 **1038:** circlip pliers bent, external $\bullet$ 175 mm
n. 100 **861/C100:** For manual, electric and pneumatic screwdrivers $\odot \odot \oplus \oplus \bullet \bullet$
 $\oplus \oplus \odot \odot$
n. 1 **1048N:** slip joint pliers, slip-proof PVC coated handles 250 mm

