



Performance Plus Duct Tape

8979

Technical Data

June, 2010

Product Description 3M™ Performance Plus Duct Tape 8979 has a unique product construction for indoor and outdoor applications. This tape is removable with little or no adhesive residue from most opaque surfaces up to six months after application. 3M™ Performance Plus Duct Tape 8979 is also resistant to delamination and deterioration when exposed to UV outdoors for up to one year.

Product Construction	Backing	Adhesive	Colors	Standard Roll Lengths
	Polyethylene film	Rubber	Black, Olive,	54.8 m (60 yds.)
	over cloth scrim		Slate Blue	22.9 m (25 yds.)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		ASTM Test Method
Adhesion to Steel:	48 oz./in. width (53 N/100 mm)	D-3330
Tensile Strength:	36 lbs./in. width (630 N/100 mm)	D-3759
Elongation at Break:	19%	D-3759
Tape Thickness:	12.1 mils (0.31 mm)	D-3652
Temperature Use Range:	Up to 200°F (93°C)	

Features

- Tested in accordance with UL 723 / ASTM E84.
- Backing is curl resistant, moisture resistant and conformable making the tape easy to handle and apply.
- High tensile strength for the most demanding applications.
- Hand-tearable.
- Rubber adhesive bonds well to many surfaces with excellent initial stick.
- Unwinds easily from the roll to minimize user fatigue.
- Distinctive slate blue color available.

3M™ Performance Plus Duct Tape

8979

Application Ideas

- Ideal for demanding duct tape applications in the construction, electrical, industrial, marine and military markets.
- Applications for sealing, holding, identification and protection.
- Maintenance Repair and Other (MRO) applications for patching, bundling, reinforcing, tabbing and temporary repair.
- Taping and splicing insulation, capping pipe and conduit ends, marking and labeling.
- Hanging polyethylene drapes, industrial masking and light sandblast overspray protection.

Storage

Store under normal conditions of 70°F (21°C) and 50% R.H. in the original carton.

Shelf Life

To obtain best performance, use this product within 18 months from date of manufacture.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2010 70-0709-5360-2 (6/10)