

## Features

- 8.2mm/sec maximum speed
- 200mm Stroke length
- Quiet operation
- IP54 protection
- Preset limit switches

## RS PRO 24V DC Micro Linear Actuator

RS Stock No.: 177-4502



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

*A compact but powerful electric linear actuator for precise movement in a linear motion. They are ideal for applications where installation space is limited, such as a window opener or an adjustable car driver.*

*An electric linear actuator is a versatile device capable of pushing and pulling along with the ability to slide, tilt, lift and drop.*

## General Specifications

Actuation Type	Micro Linear Actuator
Colour	RAL 7035
Duty Cycle	10% or 2 min of continuous operation in 20 min.

## Electrical Specifications

Input Voltage	24VDC
Maximum Load	3000N (Push) / 3000N (Pull)
Maximum Speed	8.2mm/s @ 3000N
Noise Level	5

## Mechanical Specifications

Maximum Stroke Length	200mm
-----------------------	-------

## Protection Category

IP Rating	IP54
-----------	------

## Similar Products

Push (N)	Pull (N)	No Load Speed (mm/s)	Full Load Speed (mm/s)	Stroke (mm)	RS Stock No
3000	3000	11	8.2	200	177-4502
3000	3000	11	8.2	100	177-4506
3000	3000	11	8.2	400	177-4507
3000	3000	11	8.2	100	177-4508

