




MSP-15-SS

Ruland MSP-15-SS, 15mm Two-Piece Shaft Collar, 303 Stainless Steel, Clamp Style, 34mm OD, 13mm Width



Description

Ruland MSP-15-SS is a two-piece shaft collar with a 15mm bore, 34mm OD, and 13mm width. The clamp style design does not mar the shaft, is easy to remove, and is indefinitely adjustable. MSP-15-SS is commonly used for guiding, spacing, stopping, mounting, and component alignment. Equipment manufacturers benefit from the tightly controlled face to bore perpendicularity of Ruland shaft collars, TIR of ≤ 0.05 mm. Perpendicularity is critical for alignment when the shaft collar is used as a load bearing face, mechanical stop, or for mounting components such as gears or bearings. Proprietary processes have been developed by Ruland to maintain superior fit, finish, and holding power. MSP-15-SS is stamped with the Ruland name and bore size for ease of identification. Halves are mated throughout the manufacturing process for proper fit and alignment. Forged screws test beyond DIN 912 12.9 standards to ensure maximum holding power. MSP-15-SS is machined from solid bar stock to a fine burr free finish and sourced exclusively from North American mills. Ruland uses 303 stainless steel with hardware of like material for consistent corrosion resistance. Stainless steel hardware undergoes a proprietary surface treatment process to prevent galling. It is RoHS2 and REACH compliant and manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore B	15 mm	Bore Tolerance	+0.050 mm / +.012 mm
Outer Diameter OD	34 mm	Clearance Diameter C MAX	39.3 mm
Width W	13 mm	Width Tolerance	+0.076 mm / -.254 mm
Forged Clamp Screw	M5x16	Screw Material	18-8 300 Series Stainless Steel
Hex Wrench Size	4.0 mm	Screw Finish	Bright
Seating Torque	5.4 Nm	Screw Location R	12.50 mm
Number of Screws	2 ea	Material Specification	Type 303 Austenitic, Non-Magnetic Bar
Temperature	-40°F to 350°F -40°C to 176°C	Finish Specification	Bright
Country of Origin	USA	Weight (lbs.)	0.1600
UPC	63452901539		