

6 ft Black SuperSpeed USB 3.0 Cable A to B - M/M

Product ID: USB3SAB6BK



StarTech.com's 6ft Black SuperSpeed USB 3.0 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the 6ft USB 3.0 cable offers a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 6ft USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 6ft USB 3.0 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility



Applications

- Connect a SuperSpeed USB 3.0 device to an USB 3.0 capable PC, Notebook, or Server

Features

- Designed and constructed to SuperSpeed USB 3.0 Specifications
- Molded connectors with strain relief

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Foil shielded twisted pair
Performance	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)	Connector A	1 - USB Type-A (9 pin) USB 3.0 Male
	Connector B	1 - USB Type-B (9 pin) USB 3.0 Male
Environmental	Humidity	0~75% RH
	Operating Temperature	-10°C to 50°C (14°F to 122°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Color	Black
	Product Length	6 ft [1.8 m]
	Weight of Product	3.1 oz [87 g]
	Wire Gauge	28 AWG
Packaging Information	Package Height	0.9 in [24 mm]
	Package Length	8.9 in [22.5 cm]
	Package Width	4.9 in [12.5 cm]
	Shipping (Package) Weight	3.2 oz [92 g]
What's in the Box	Included in Package	1 - 6ft black USB 3.0 A to B cable

Product appearance and specifications are subject to change without notice.