



Product Information

DIK125x32-Ø8

EAN 4031582070163

Wheel centre made of pressed steel, Tread: solid rubber, grey non-marking, with threadguards, cone ball bearing

Wheel diameter	125 mm
Width of Tread	32 mm
Axle Hole Ø	8 mm
Hub length	36 mm
Temperature	- 20 / + 85 °C
Standard	EN 12530
Weight	0.614 kg
Dynamic Load capacity	100 kg
Static Load capacity	200 kg
Hardness of tread	A 80 Shore

