

Solenoid valve

VZWD-B-L-M22C-M-G14-15-V-36-2A-A1-80-R1

Part number: 8214486

FESTO



 General operating condition

Data sheet

Feature	Value
Design	Directly actuated poppet valve
Type of actuation	Electrical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Inline installation
Connection Process valve	G1/4
Electrical connection	Plug To EN 175301-803 Square design
Nominal size	1.5 mm
Valve function	2/2-way, single solenoid, closed
Manual override	None
Flow direction	Non-reversible
Medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases Mineral oil Water Neutral fluids Other media on request
Pressure difference	0 MPa
Pressure difference	0 bar
Pressure difference	0 psi
Characteristic coil data	110 V AC: 50/60 Hz, pick-up power 40.0 VA, holding power 30.0 VA
Insulation material class	H
Permissible voltage fluctuations	+15% / -10%
Duty cycle	100%
Type of reset	Mechanical spring
Type of piloting	Direct
Symbol	00992979
Medium pressure	0 MPa ... 8 MPa
Medium pressure	0 bar ... 80 bar

Feature	Value
Medium pressure	0 psi ... 1160 psi
Max. viscosity	25 mm ² /s
Media temperature	-10 °C ... 140 °C
Ambient temperature	-10 °C ... 80 °C
Flow rate Kv	0.07 m ³ /h
Switching time on	8 ms
Switching time off	25 ms
Note on materials	RoHS compliant
Material housing	High-alloy stainless steel
Material number housing	1,4305
Material seals	Fluoro rubber
Product weight	440 g
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
Degree of protection	IP65
Corrosion resistance class CRC	3 - high corrosion stress