



### Main

Range	Resi9
Product or component type	Insulation bottom
Accessory / separate part category	Insulation accessory
Range compatibility	Opale enclosure Resi9 enclosure

### Complementary

Number of horizontal rows	4
Number of 18 mm modules per row	18
Total number of 18 mm modules	72
Provided equipment	1 bakelite bottom 4 plug 4 screw
Net weight	350 g
Width	625 mm
Height	357 mm
Depth	3 mm

### Environment

Fire resistance	750 °C conforming to EN/IEC 60695-2-11
IP degree of protection	IP30 conforming to EN/IEC 60529
IK degree of protection	IK08 conforming to IEC 62262 IK08 conforming to EN 50102
Overvoltage category	Class II

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>