



Main

Range	MasterPacT
Range of product	MasterPact NT MasterPact NT NAVY ComPact NS630b...1600 new generation
Device short name	MN
Product or component type	Voltage release
Device application	Control
Voltage release type	Opening coil Undervoltage release
Control type	Standard
[Uc] control circuit voltage	200...250 V AC 50/60 Hz 200...250 V DC
Circuit breaker mounting mode	Drawout
Range compatibility	Masterpact MasterPact NT ComPact ComPact NS630b...1600

Complementary

Operating threshold	0.35...0.7 x Un opening 0.85 x Un closing
Response time	40 ms +/- 5 % for MasterPact NT 90 ms +/- 5 % for Compact NS630b...1600
Supply holding power	4.5 VA

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information