

Datasheet

High Speed, Molybdenum Steel Step Drill Bit

RS Stock number [232-541](#)



Description:

High speed steel step drills for rapid drilling and deburring in sheet materials up to 3mm thick. Eliminates vibration and chatter and provides clear holes in applications requiring small hole size increments in stainless steel, aluminium, plastic etc.

Specifications:

Drill Diameter:	4 – 12 mm
Material:	High Speed Molybdenum Steel
Maximum Drilling Thickness:	3 mm
Number of Steps:	8
Increments:	1 mm
Surface:	Bright Finish