



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: DEC 2011 (71) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #5-103911-3
60 SYSTEM 50 RCPT ASSY DRRA

TE Part #5-104076-2
60 SYS50 HDR DRST SHRD W/SL SN

TE Part #2176314-4
MELF SMA_A 180R 0.1% 15PPM 0102 0.3W

TE Part #3-1415020-1
PT570N20

TE Part #3-2319848-1
END STACK DIP 10P G RECESS SEAL TUBE

TE Part #5146893-2
1FHR,84,30A/S,S,C,S08,09,10

TE Part #1-928836-2
MOD2 PIN WITH A-PIN L/P

TE Part #1-1437581-1
ASE22RL=AUTOSLIDE DP

TE Part #4-2176391-7
RQ 1206 37K4 0.1% 10PPM 5K RL

TE Part #7-2176246-6
CRGS2512 5% 1M8

Documents

Product Drawings

STEP-Z PLUG 25MM 296P PB ST

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-1761616-5_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1761616-5_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1761616-5_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



STEP-Z Interconnection System

English

Product Specifications

Product Specification

English