



3852 Ratchet Crimping Pliers modular plugs

Item Number	Icon	Length
430028		250mm

Designed for the safe and secure attachment of modular plugs type 8P8C (RJ-45) 6P6C (RJ-12) and 6P4C (RJ-11), cuts, strips & crimps all types without change of die. Built in wire stripper on the front and cutter on the reverse featuring a guide for precise length wire stripping.



3698 Ratchet Crimping Pliers COAX - BNC, TNC

Item Number	Icon	Length
430026		230mm

For: 58, 59, 62, 8X, 140, 141, 174, 210, 223, 303, 400.

Tested to 40,000 cycles,
guaranteed for 30,000 cycles.



3645 Crimping Pliers for ferrules

Item Number	Icon	Length	mm ² /AWG
430005		145mm	0.25 - 2.5 / 23 - 13

Matt chrome plated for corrosion resistance. Contoured grips with anti-slip horns for comfort and safety.



3646 Crimping Pliers for ferrules

Item Number	Icon	Length	mm ² /AWG
430006		220mm	0.5 - 16 / 20 - 5

Matt chrome plated for corrosion resistance. Contoured grips

Our customers are currently enjoying:

- Same day despatch
- 98% stock availability
- 24 hour online ordering



For our comprehensive range of electrician's pliers & cutters, please see pages 14-16.



C.K tools has various ranges of screwdrivers for different uses.

Our SensoPlus VDE range is for professional electricians and guarantees safe working on electrical equipment up to 1000V. We have the Triton ESD and Xonic ESD ranges for electronics assembly work where ESD functionality is a requirement. For general purpose users, such as construction or engineering professionals, we have our sensoplus range, with dual compound soft-grip handles, or the HD Comfort range with

wipe-clean acetate handles. Finally, we have the Precision range which are ideal for use on intricate work.

We have the right range for many different users.

What doesn't change is the highest standards of materials and manufacturing processes that we use to make them.

