



17 mm 1/2" impact socket deep - 1pc

SHOCKWAVE™ IMPACT DUTY IMPACT SOCKETS

- SHOCKWAVE™ IMPACT DUTY steel (Chrome-Molybdenum) is high quality alloy steel which provides ultimate strength and durability.
- Best fitting thanks to 6 gripping points.
- Non-slip hex geometry to prevent socket and fastener rounding.
- Deep wall construction provides clearance for protruding bolts.
- Stamped and ink filled diameter markings and laser etched part number for wear resistance.
- Dual hole design and groove for security accessories.



ø (mm)	26.2
Article Number	4932480335
For anchor rod thread size	M10 (DIN)
Pack quantity	1
Size AF [across flats][mm]	17
Tool reception	½" square
Total length (mm)	78
Working depth [mm]	9.8
Working length (mm)	9.8