


# GROMMETS & BUSHINGS, LED SPACERS AND INSULATORS

G

Part No.	"A" mm	"B" mm	"C" Max. mm	Wall thickness
DSC-0.5	1.6	7.6	0.8	0.8
DSC-1	3.2	9.5	0.5	1.2
DSC-2	4.8	12.7	0.8	
DSC-3	6.4	15.9	1.1	1.6



**DCS**

DURO STRIP CHANNEL

Material: Nylon 6 - grey; RMS-21

Note:

DSC	1
Part	Type