

## Metal tool box with assortment, 193 pieces 1/4 " + 3/8", inch sizes, 1483KHD3RB-FF3



Article number: 1483KHD3RB-FF3

Size: 523x257x300cm

Weight: 11,000 g

Packing quantity: 1pc. "

193-piece Metal tool case with range 1/4 " + 3/8".

- Drawers fully extendable
- Reinforcement of the lid by corrugated aluminium plate for a secure footing
- Lid handle and stable side handles for safe transport
- Drawers locking system

### Lid Compartment – 5 pieces



|                                      |        |
|--------------------------------------|--------|
| 481-400<br>Hammer                    | 400g   |
| 3625N-35<br>Superflex plastic hammer | 415g   |
| 2509<br>Flexible gripper             | 525 mm |
| 2535F2<br>Magnetic lifter            | 1kg    |
| 7762<br>Extension 3/8 "              | 250mm  |

## Foam insert socket wrench 1/4 ", 3/8", 95-piece



|   |            |  |
|---|------------|--|
| inserts 1/4 ", double Short               | 6700SM     | 5.5, 6, 7, 8, 9, 10, 11, 12, 13                        |
| inserts 1/4 ", double Long                | A6800DM    | 5.5, 6, 7, 8, 9, 10, 11, 12, 13                        |
| Screwdriver bits 1/4 "                    |            |  |
| for hexagon socket screws                 | 6709M      | 3, 4, 5, 6, 8  |
| Screwdriver bits, 1/4 "for Phillip screws | 6709PH     | PH1, 2, 3  |
| Screwdriver bits, 1/4 "for TORX® screws   | 6709TORX   | T8, T9, T10, T15, T20, T25, T27, T30, T40              |
| Ratchet 1/4 "Narrow head                  | 6950SL     | -  |
| T-handle 1/4 "                            | 6954       | -  |
| Drive handle 1/4 "                        | 6956       | -  |
| Flexible handle 1/4 "                     | 6958       | -  |
| Renewals 1/4 "                            | 6960/6961/ | 50, 100,   |
|   | 6962/6962L | 150, 355 mm  |
| Universal joint 1/4 "                     | 6966       | -  |
| Bit holder 1/4 "                          | 6972H      | -  |
| 3/8 "to 1/4" transitional part            | 7764       | -  |
| Sockets, 3/8 "6-point, short              | 7400SM     | 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 22 |
| Sockets, 3/8 "double-6kant, Long          | A7402DM    | 10, 11, 12, 13, 14, 15, 16, 17, 18, 19                 |
| Screwdriver bits, 3/8 "                   |            |  |
| for hexagon socket screws                 | 7409M      | 3, 4, 5, 6, 7, 8, 10                                   |
| Screwdriver bits, 3/8 "for TORX® screws   | 7409TORX   | T25, T27, T30, T40, T45, T50                           |
| Ratchet 3/8 "Narrow head                  | 7750SL     | -  |
| T-handle 3/8 "                            | 7754       | -  |
| Flexible handle 3/8 "                     | 7758       | -  |
| Renewals 3/8 "                            | 7760/7761  | 75, 125 mm   |
| Universal joint 3/8 "                     | 7766       | -  |
| 1/4 "to 3/8" transitional part            | 7765       | -  |
| 3/8 "to 1/2" transitional part            | 8164-1 / 2 | -  |
| Bit holder 3/8 "                          | 7407H      | 1/4 " - 3/8"   |
| Bit-ratchet 1/4 "                         | 2058-BR    | -  |
| Feeler gauges                             | 1544       | -  |

## Foam insert Screwdriver, 53-piece



|  |                     |                                    |
|--|---------------------|------------------------------------|
| Screwdriver with pistol grip                                   | 808050P             | -                                  |
| Screwdriver, short version                                     | 808050S             | -                                  |
| Bit-Box, 31-piece set  | 59 / S31-1          | -                                  |
| Double angled offset<br>screwdriver for slotted screws         | 2047-0.8-4          | 0,8x4x100                          |
| Double angled offset<br>screwdriver for Phillips screws        | 2047PR-1-2          | PH1, 2                             |
| Ergo screwdriver for slotted screws                            | BE-8020L            | 0,5x3x75                           |
| Ergo screwdriver for slotted screws                            | BE-8030             | 0,6x3,5x75                         |
| Ergo screwdriver for slotted screws                            | BE-8155             | 1,2x6,5x125                        |
| Ergo screwdriver for slotted screws,<br>hex shaft and approach | BE-8260             | 1,6x8,0x175                        |
| Ergo Screwdriver for slotted screws,<br>short version          | BE-8350             | 1x5,5x25                           |
| Ergo screwdriver for Phillip screws,<br>short version          | BE-8601/<br>BE 8602 | PH1x25, PH2x25                     |
| Ergo screwdriver for Phillip screws                            | BE-8610/<br>BE 8620 | PH1x75, PH2x100Angle               |
| screwdriver set, with ball, 9-piece                            | BE-9770             | HEX 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 |

## 12-piece



|   |                  |             |
|---|------------------|-------------|
| Tape measure                              | MTB-3-16-E       | 3m          |
| Ergo side cutter                          | 2101GC           | 160mm       |
| Ergo nose pliers,<br>bent, chromed        | 2427 GC-200 IP   | 200mm       |
| Ergo nose pliers,<br>long, chrome-plated  | 2430GC           | 200mm       |
| Ergo combination pliers,<br>chrome-plated | 2628 GC-160IP    | 160mm       |
| Ergo Water Pump Pliers                    | 8224CIP          | -           |
| Driver                                    | 3734             | Ø 3, 5, 8mm |
| Grains                                    | 3735-4-120       | 120mm       |
| Scriber cranked,                          | 1177-SCRIBE      | 230mm       |
| Calipers                                  | 1150-1 / 2 H / P | 150mm       |

## 28-piece



|  |          |  |
|--|----------|--|
| Combination spanner                    | BE-111M  | 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22 |
| Open-ended spanner                     | BE-6M    | 6x7, 8x9, 10x11, 12x13, 14x15, 16x17, 18x19, 20x22         |
| Ergo Adjustable Wrench 6 ", chromed    | 9070C    | 158x20 mm  |
| Telescopic articulated mirror          | 5515T-52 | Ø 50 mm  |
| Electricians knife with plastic handle | 2820EF2  | -  |
| LED Flashlight                         | BFLA01 - |  |