Features

- Maximum operating pressure is 35 bar.
- Operating temperature range -20°C to +100°C.
- Material: Brass Nickel-Plated Finish
- Single Shut Off (One side is with valve)
- Euro Profile
- DN7.2
- Flow 1000 l/min
- Compatible with:

  TST SWING COUPLING C

  TST 025

  PARKER - RECTUS 25

  CEJN 320

  JWL 520, 530

  PARKER PE

RS PRO Pneumatic Quick Connect Coupling

RS Stock No.: 0325360

RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Pneumatic Quick Connect Couplings

Product Description

RS PRO Series 26 Quick Connect Couplings
Pneumatic quick-connect coupling connectors are found across industry in pneumatic systems as diverse as robotic assembly lines and other equipment.

- Maximum operating pressure is 35 bar.
- Operating temperature range -20°C to +100°C.
- Material: Brass Nickel-Plated Finish
- Single Shut Off (One side is with valve)
- Euro Profile
- DN7.2
- Flow 1000 l/min
- Compatible with:
  TST SWING COUPLING C
  TST 025
  PARKER - RECTUS 25
  CEJN 320
  JWL 520, 530
  PARKER PE

Specifications

Manufacturer Series	026
Coupling Type	Quick Connect Coupling Plug
Connection Standard	DN 7.2 Euro Profile
Connection Standard Compatible With	TST 025; PARKER RECTUS 25, CEJN 320; JWL 520 & 530; PARKER PE
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+100°C
Maximum Operating Pressure	35bar
Flow	1000 l/min
Flow Direction & Sealing	Through Type Coupling
Material	Brass
Finish	Nickel Plated
Connection Type	Threaded
Thread Size	1/2 in
Thread Standard	G
Thread Gender	Female
Coupling Gender	Female
Threaded Connection	G 1/2 Female
Seal material	N/A
Hose Barb Connection	N/A

Pneumatic Quick Connect Couplings

Specifications



Dimensions (mm)		
SW	L	ØD
24	36	-



Material Code

A = Brass Nickel Plated

B = Brass Nickel Plated

C = Brass Nickel Plated

S = Brass Nickel Plated







Series 26 Quick Connect Couplings

0 - 35 bar (0-508 PSI)	-20° to + 100°C (NBR) -4° to + 212°F
Shut Off Type	
OM 262 - 00990 OM 200 - 00650	FLOW 1000 lt/min
DN 7.2 mm	