

## ITX K 19 T40

### Impact socket 1/2"

for recessed TX head screws

Code	ETIM
<b>6197360</b>	<b>EC002213</b>
EAN	UNSPSC
<b>4010886619735</b>	<b>27-11-17-04</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-02-90</b>
Customs tariff number	
<b>82079030</b>	



### Article description

- Square drive as per DIN 3121 - G 12,5, ISO 1174
- GEDORE special steel, manganese-phosphated

### Article information

Contents (Qty of pieces)	1	Backup	Circlip and pin
Net weight [kg]	0,077 kg	Insertion depth 1	26,0 mm
Total length [mm]	47 mm	Insert-Ø 1	25,0 mm
Surface	manganese phosphated	Actuation type	machine-operated
Material	Steel	Tip size TX (recess)	T40
Drive connector square female (metric)	12,5 mm	Screw size	M7 - M8
Drive connector square female [inch]	1/2"	Tip size TX (recess) [mm]	6,65 mm
Standard	DIN 3121 - G 12,5 ISO 1174		