

BK-4MCDE CASE

eneloop AAA (Standard) — Case Pack



Key Specifications

Parameter	Value
Part Number	BK-4MCDE CASE
Cell size	AAA (Micro)
Chemistry	Ni-MH, LSD
Nominal voltage	1.2 V
Capacity (typ. / min.)	800 mAh / 750 mAh
Rechargeable cycles	Up to 2,100 times
Charge retention	70% after 10 years storage
Weight	≈12 g per cell
Operating temperature	0°C to 50°C
Pack type	Bulk/case carton — multiple retail 4-packs per case