

Description

STAINLESS STEEL TOP PLATE CASTOR, RED POLYURETHANE 150MM

Fixed

KF4BA150-28L

Part Number

Swivel


KP4BA150-28L

Swivel and brake

KP4BD150-28L



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	150 mm		
Overall Height H	183 mm ±1		
Size of plate A X B	105 x 85 mm±1		
Plate hole centres a x b	80 x 60 mm±0,3		
Plate hole	9 mm		
Offset F ±1	\	45 mm	45 mm
Width of Tread	40 mm±0,5		
Hardness of tread	shore A ± 98		
Load capacity	180 Kg		
Weight	0,80 kg	1,03 kg	1,25 kg
Temperature	- 20 / + 60 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
Fastening by top plate.
Total lock. Metal pedal.

Wheel :

Wheel centre made of White Polyamide.
Tread : Red injected Polyurethane non marking.
Hub : Plain bore.

Features :

Low starting effort. High load capacity.
Lightweight, highly resistant to knocks and other impacts, abrasion as well as a great many chemical substances.
Corrosion resistant, easy to clean. Specially designed for humid environments.
Suited for Food industry, Hospital or Industrial Kitchen equipment.
Non staining red tyre.
Medium duty.