

Datasheet

RS Pro LED Machine Light, 100 to 260 V ac, 24 W

RS Stock No: **777-7965**



Product Details

RS Pro LED machine light minimizes eyestrain and delivers efficient lighting. This LED strip light allows positioning in lighting angles such as 40°, 60° and the standard 80°. It is perfect for application such as semiconductors manufacturing equipment and clean rooms.

Features and Benefits

- Reinforced lens for high resistance
- Furnished with 1.8 m cord with Euro plug
- Long service life up to 40,000 hours
- Temperature range of -30° to +60°
- Aluminium body



Specifications:

Cable Length	1.8 m
EU Energy Efficiency Rating	A+
IP Rating	IP67
Lamp Supplied	Yes
Lamp Type	LED
Voltage Rating	AC100-240V
Wattage	24 W
Beam Angle	80°