

LEVINA

5320PJP075P41-38x38/10

EAN 4031582410563

Swivel castor, housing and wheels made from high grade synthetic materials, with integrated threadguards, plate fitting. Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, precision ball bearing , with threadguardsThe castor meets all requirements for EN 12530, except for swivel play.



Picture may differ from original product

Technical Data

Wheel diameter	75 mm
Wheel width	25 mm
Castor width	44 mm
Size of Plate	60 x 60 mm
Plate hole centres	48/38 x 48/38 mm
Plate hole	6,3 mm
Dome-Ø	44 mm
Offset	27 mm
Swivel Interference	129 mm
Overall height	103 mm
Temperature	- 10 / + 40 °C
Standard	EN_12530
Weight	0.242 kg
Swivel Radius	64.5 mm
Hardness of tread	Shore A 87
Load capacity	75 kg
Load capacity (static)	150 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

LEVINA

5320PJP075P41-38x38/10

EAN 4031582410563



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

