



6015DDU

Single-Row Deep Groove Ball Bearings

Parts Number

6015DDUC3

Boundary Dimensions

d	75	mm	Bore diameter
D	115	mm	Outside diameter
B	20	mm	Width
r (min.)	1.1	mm	Chamfer dimension

Basic Load Ratings

Cr	43500	N	Basic dynamic load rating
C0r	33500	N	Basic static load rating

Speeds

Grease	3400	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	81.5	mm	Diameter of shaft abutment
da (max.)	85.5	mm	Diameter of shaft abutment
Da (max.)	108.5	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet
Dx (min.)	0	mm	Diameter of snap ring recess in the housing
Cy (max.)	0	mm	Distance from outer ring side face to snap ring back face

Calculation factors

fo	15.8		Factor
----	------	--	--------

Additional information

z	15		Number of Balls
Dw	11.906	mm	Ball Diameter

Mass

Mass approx.	0.649	kg	Mass approx.
--------------	-------	----	--------------

