

# Eaton 136262

Catalog Number: 136262

Eaton Moeller® series CSAR Connection cable, 3p, AC, coupling m12 angled, open end, L=2m

General specifications



| Product Name                         | Catalog Number |
|--------------------------------------|----------------|
| Eaton Moeller® series CSAR Accessory | 136262         |
| Connection cable                     | EAN            |
|                                      | 4015081330553  |
| Product Length/Depth                 | Product Height |
| 165.1 mm                             | 12.7 mm        |
| Product Width                        | Product Weight |
| 165.1 mm                             | 0.09 kg        |
| Certifications                       |                |
| CE                                   |                |

## Product specifications

### Type

Connecting cables

### Number Of Poles

Three-pole

### Cable type

Coupling, angled, Input side

Cable end, open, Output side

Multi-core

### Contact surface material

Other

### Rated operational voltage (Ue) - max

0 V

### Product category

Accessories

### Voltage type

AC

### Ambient operating temperature - max

70 °C

### Ambient operating temperature - min

-25 °C

### Continuity resistor

0 mΩ

### Nominal current

0 A

### Cable length

2 m

### Cable sheath material

Other

### Degree of protection

Other

### Color cable sheath

Yellow

### Electrical connection type (box-sided)

Other

### Electrical connection type (field-sided)

M12

## Resources

### Catalogs

[Product Range Catalog Sensors – products, basic information, applications](#)

### Drawings

[eaton-proximity-switches-csdr-connecting-cable-3d-drawing.eps](#)

### Multimedia

[We make what matters](#)

### Wiring diagrams

[eaton-proximity-switches-csas-connecting-cable-wiring-diagram.eps](#)

Contact body material

Other

Permitted temperature of outer cable (assembled) without vibration - max

70 °C

Permitted temperature of outer cable (assembled) without vibration - min

40 °C

Permitted temperature of outer cable (assembling/handling) - max

70 °C

Permitted temperature of outer cable (assembling/handling) - min

40 °C

Plug-in contact type (box-sided)

Male (plug)

Plug-in contact type (field-sided)

Female (bus)

Positioning cable feed (box-sided)

Other

Positioning cable feed (field-sided)

Angled



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia