



ENGLISH

Datasheet

136-8577

CT2690 LAN Cable Solution Multifunction Tester



RS Article No.	Body type	Kind of Cable Tester	Conditions of Cable Tester	Display	Operating way	Battery type
136-8577	Plastic	LAN, TEL, COAX	PASS, OPEN, SHORT, CROSS, SPLIT.	Graphic LCD	Rubber Keypad	Alkaline 9VDC



SPECIFICATIONS:

Display:	LCD Module (64 mm x 33 mm)
Connector Type:	RJ45, RJ12 (RJ11) & F connector
Cable Type:	Shielded or unshielded, CAT -5, CAT-6, CAT-7
Error Status:	OPEN, SHORT, CROSS, SPLIT
Measure Technology :	Measures cable length via TDR to goal that.
Length for Test:	1~350 meters (3~1200 feet)
Power Source:	9VDC Battery.
Operating Temperature:	0° to 50° C (32° to 122° F)
Storage Temperature:	-10° to 60° C (14° to 140° F)
Humidity:	10 % to 90 % non-condensing
Dimension:	195 mm (L) , 90 mm (W) , 40 mm (H)
Certification:	CE, RoHS