





Assembly example: UM108-SEFE/R



General Information:

- Simplified representation
- Document excluded from change process
- Linear dimensions [mm]
- Tolerances apply in a normal climate according to DIN EN ISO 291-23/50-2, PA plastic parts with about 2% (% by weight) moisture content.
- Web: www.phoenixcontact.com

Additional Information:

- A) Mounting rail like EN 6075: TH 35-7,5/15 or mounting rail TH 35-15x1,5 similar to EN 60715
- B) PCB level 1
- C) PCB level 2
- D) Holes for Ø3 screws
- E) Labeling area
- F) Marker groove for zack marker strip
- G) Pozidriv recessed head PZ1
- Recommended PCB-outline see further documentation

KIT (not mounted)					
Pos.	QTY	description		material	
1	1	SIDE ELEMENT LEFT		PA	
2	3	PAN HEAD SCREW 3X14-Z		STL	
		document-No. / RI		date	scale
		00893536 / 01		13.07.2018	2:1
		ident.-No.	document-type		
		2959683	TECDOC 2D_Productdrawing		
		description			
		UM108-SEFE/R			
page 1		of 1			