

CA-12F1N8A85DUSX - Cable connector



1243590

<https://www.phoenixcontact.com/in/products/1243590>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, SPEEDCON, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 3 mm ... 14.5 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable connection solutions in the industrial environment
- Reduced connection time with SPEEDCON fast locking system
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

Item number	1243590
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRAEB
GTIN	4063151473525
Weight per piece (including packing)	96.6 g
Weight per piece (excluding packing)	96.6 g
Customs tariff number	85366990
Country of origin	DE

CA-12F1N8A85DUSX - Cable connector



1243590

<https://www.phoenixcontact.com/in/products/1243590>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
Order information:	When using a specific cable with Ø 3 mm ... 4 mm, it may be necessary to use the special cable seal (1786600)

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Connection 1

Head design	Socket
-------------	--------

Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Insulation body material	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Feedback, signal
	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Contact diameter	1 mm
Litz wire cross-section	0.06 mm²
Litz wire cross-section	1 mm²
Nominal current per signal contact	8 A
Rated voltage Signal contact	48 V AC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Housing material	Metal
Type of locking	SPEEDCON
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal

External cable diameter	3 mm ... 14.5 mm
-------------------------	------------------

CA-12F1N8A85DUSX - Cable connector



1243590

<https://www.phoenixcontact.com/in/products/1243590>

Seal material	FPM
---------------	-----

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

CA-12F1N8A85DUSX - Cable connector




1243590

<https://www.phoenixcontact.com/in/products/1243590>

Drawings

Schematic diagram



Contact chamber numbering (view of plug-in side), standard socket

CA-12F1N8A85DUSX - Cable connector



1243590

<https://www.phoenixcontact.com/in/products/1243590>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1243590>

cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	6 A	18	-

UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	8 A	18	-

cULus Recognized				
------------------	--	--	--	--

CA-12F1N8A85DUSX - Cable connector



1243590

<https://www.phoenixcontact.com/in/products/1243590>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

CA-12F1N8A85DUSX - Cable connector



1243590

<https://www.phoenixcontact.com/in/products/1243590>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

CA-12F1N8A85DUSX - Cable connector



1243590

<https://www.phoenixcontact.com/in/products/1243590>

Accessories

SF-10KS0,06-1,00 - Crimp contact

1241922

<https://www.phoenixcontact.com/in/products/1241922>



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.06 mm² ... 1 mm², Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

RF-Z0014 - Color coding

1620588

<https://www.phoenixcontact.com/in/products/1620588>

Color coding, color: green



CA-12F1N8A85DUSX - Cable connector

1243590

<https://www.phoenixcontact.com/in/products/1243590>




RF-Z0015 - Color coding

1620592

<https://www.phoenixcontact.com/in/products/1620592>

Color coding, color: orange



RF-Z0016 - Color coding

1620593

<https://www.phoenixcontact.com/in/products/1620593>

Color coding, color: black



CA-12F1N8A85DUSX - Cable connector

1243590

<https://www.phoenixcontact.com/in/products/1243590>



RF-Z0003X - Square mounting flange

1242369

<https://www.phoenixcontact.com/in/products/1242369>



Square mounting flange, Axial seal, 4xM3, flange dimensions: 35 mm x 35 mm, series: RF, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/in/products/1607456>



Torque screwdriver, series: RC, UC, SH, SF

CA-12F1N8A85DUSX - Cable connector

1243590

<https://www.phoenixcontact.com/in/products/1243590>



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/in/products/1607455>



Hook wrench, series: RC, UC, RF, SF

PROT-M23-SG-IT-IP20 - Plastic protective cap

1577206

<https://www.phoenixcontact.com/in/products/1577206>



Plastic protective cap, M23, series: CA, RC, RF, UC, RM

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in