

# Product data sheet

Specifications



Repacked, triple socket-outlet,  
Mureva Styl, 2P + E with shutters,  
pin earth, 16A, 250V, surface,  
anthracite

MUR36037W



This repacked option saves 2.303 over the  
standard condition

## Main

|                             |                       |
|-----------------------------|-----------------------|
| Range                       | Mureva Styl           |
| Range of product            | Mureva Styl           |
| Product or component type   | Socket-outlet         |
| Device presentation         | Complete product      |
| Outlet poles configuration  | 2P + E                |
| Outlet standard description | Pin earth             |
| Outlet standard deviation   | French                |
| Colour tint                 | Anthracite (RAL 7016) |

## Complementary

|                                |                                                                                                                                              |
|--------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| Device mounting                | Surface                                                                                                                                      |
| Socket number                  | 3                                                                                                                                            |
| Rated current                  | 16 A                                                                                                                                         |
| [Ue] rated operational voltage | 250 V AC                                                                                                                                     |
| Condition of use               | Indoor/outdoor                                                                                                                               |
| Material                       | PP (polypropylene)<br>PC (polycarbonate)<br>Brass                                                                                            |
| fixing mode                    | Screws                                                                                                                                       |
| Clamping connection capacity   | 1...2.5 mm <sup>2</sup> for rigid cable(s)<br>1...2.5 mm <sup>2</sup> for stranded cable(s)<br>1...2.5 mm <sup>2</sup> for flexible cable(s) |
| Wire stripping length          | 13 mm                                                                                                                                        |
| Cable entry                    | Easy valve access diameter: 6...12 mm                                                                                                        |
| Height                         | 76 mm                                                                                                                                        |
| Width                          | 218 mm                                                                                                                                       |
| Depth                          | 64 mm                                                                                                                                        |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                            |                                           |
|--------------------------------------------|-------------------------------------------|
| Chemical and detergent products resistance | Resistant to alcohol (70 %)               |
|                                            | Resistant to alcohol (96 %)               |
|                                            | Resistant to A-Lactic Acid                |
|                                            | Resistant to diluted quaternary ammonium  |
|                                            | Resistant to diluted bleach               |
|                                            | Resistant to diluted ammonia              |
|                                            | Resistant to soapy water                  |
|                                            | Resistant to crystal cleaner              |
|                                            | Resistant to hydrogen peroxide 10 volumes |
|                                            | Resistant to hexane                       |
| Outlet standard                            | CEE 7/5                                   |
| surface treatment                          | Untreated                                 |
| Surface finish                             | Matt                                      |
| [Ue] rated operational voltage             | 250 V                                     |
| Network frequency                          | 50/60 Hz                                  |
| Connections - terminals                    | Screw terminals                           |

## Environment

|                                       |                                                       |
|---------------------------------------|-------------------------------------------------------|
| Quality labels                        | NF                                                    |
| IP degree of protection               | IP55                                                  |
| IK degree of protection               | IK08                                                  |
| Flame retardance                      | Self-extinguishing 650 °C conforming to IEC 60695-2-1 |
| Ambient air temperature for operation | -5...40 °C                                            |
| Ambient air temperature for storage   | -25...55 °C                                           |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 6.500 cm  |
| Package 1 Width              | 7.500 cm  |
| Package 1 Length             | 22.000 cm |
| Package 1 Weight             | 388.000 g |
| Unit Type of Package 2       | S03       |
| Number of Units in Package 2 | 16        |
| Package 2 Height             | 30.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 6.684 kg  |

## Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Lower carbon footprint

2 kg CO2 eq.

## Use Better



### Materials and Substances

SCIP Number

52b60409-d705-46c7-9ba3-cc3ef6e307da

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

## Use Longer



### Lifetime extension

Repair

No

## Use Again



### Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins