

ST-H Ultrasonic level transducer: continuous, non-contact, 0.3 - 10m (1-33ft) range, for liquids. Process connection: ETFE, R 2" (BSPT), EN 10226) Cable length: 10 m (32.81 ft) . Approvals: CSA Class I, II, III, Div. 1, Groups A, B, C, D, E, F, G T3; ATEX II 2G Ex mb IIC T5 Gb, Ta = -20°C to +60°C; UKEX II 2G Ex mb IIC T5 Gb, Ta = -20°C to +60°C; INMETRO Ex mb IIC T5 Gb, -20°C ≤ Ta ≤ +60°C; RCM, KC .

Further information

Industry Online Support (Manuals, Catalogs, Certificates, FAQ, ...)

<https://support.industry.siemens.com/cs/products?mf=ps&lc=en-WW>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>

