

A43.20.063 0 °C ... 60 °C L1=40 x 9 mm alu CL.2

Bimetallic thermometer, for heating technology A43

Item number:	14138726
Quantity:	1 pcs.
Order code:	A4320063H-C1C-040ECKBB-1ZZZZZ1-KSS2ZZZ
Overview:	A43.20.063 0 °C ... 60 °C L1=40 x 9 mm alu CL.2 Case material: steel, zinc plated pointer: plastic, black Window: polystyrene, PS Thermowell: detachable, friction retained; Brass Process connection [E, d6]: G1/2B *WIKA* Dial color, 1-colored
Details:	Bimetallic thermometer, for heating technology A43 Model: A43 Design: standard, steel case Nominal size [NG, d1]: 63 mm Case material: steel, zinc plated Unit: °C Scale range: 0 °C ... 60 °C Insertion length [L1]: 40 mm Stem diameter [d5]: 9 mm Stem material: aluminum Thermowell: detachable, friction retained; Thermowell material: Brass Process connection [E, d6]: G1/2B Manufacturer logo: *WIKA* Dial printed (Number of colors): Dial color, 1-colored pointer model: plastic, black Window: polystyrene, PS Accuracy class: class 2 per EN 13190