



Product data sheet

Power tools for trade & industry

Cordless Transfer Pump

PRO GTP18V-28



The powerful and compact 18V transfer pump for various applications

The most important data

Flow rate (Standard mode)	2,800 l/h
Suction head	5 m
Delivery head	20 m

Part Number 0 601 9R6 000

Technical data

#t-productdetailpage_tools.technical-data.bi.
additional-data}

Pump System	Impeller
Flow rate (Standard mode)	2,800 l/h
Flow rate (ECO mode)	1,800 l/h
Delivery head	20 m
Suction head	5 m
Liquids	clean water
Timer	Yes
Timer settings	5/10/15 min
Connecting thread	G 3/4"
Work modes	ECO/ Standard
Self-priming	Yes
Self priming max.	5 m

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Powerful 18V water pump: Self-priming transfer pump with a flow rate of 2,800 l/h
- Versatile for different applications: With Standard and ECO working modes and a timer function
- Convenient: G3/4" external thread for hose connections
- Robust: Withstands harsh jobsite conditions and offers easy exchange of impeller

