

Features

- Premium quality Chloroprene (CR) sheet made to stringent BS 2752 specifications
- High elongation at break for greater flexibility, enhanced tensile strength for added durability
- Guarantees strong, abrasion-resistant properties
- Good weather, oil, and acid resistance (except for aromatics and ketones)
- Good weather, ageing, and oil resistance aswell as handles wear and tear effectively

RS PRO Black BS2752 Grade
Chloroprene Sheet

1000mm x 1400mm x 1mm

+120 °C to -30 °C

RS Stock No.: 0205559



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The RS PRO Chloroprene sheet is suitable for a wide range of industrial applications and environments including gaskets, seals, hoses, tubing, liners, protective sleeves.

General Specifications

Colour	Black
Material	Chloroprene
Adhesive Backing	No

Mechanical Specifications

Length	1m
Width	1.4m
Thickness	1mm
Elongation	450%
Tensile Strength	9 MPa
Hardness	40 ShA

Operation Environment Specifications

Maximum Operating Temperature	120°C
Minimum Operating Temperature	-30°C

Similar Products

Stock No	Length	Thickness	Min Operating Temperature	Max Operating Temperature
0205559	1m	1mm	-30°C	120°C
0205560	1m	1.5mm	-30°C	120°C
0205562	1m	3mm	-30°C	120°C