

Features

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins, corrosion free

RS PRO Watertight Case, Polypropylene, Black, w/Cubed Foam

RS Stock No.: 0707776,0707777,707777P



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Watertight Case, w/ Cubed Foam

For ultimate safe and secure transport, the RS PRO roller waterproof travel case provides you with superior protection from the elements, water, dust and impact when transporting fragile and valuable objects. There is a foldable pull-out handle. It is the ideal professional solution. The benefits of the RS PRO equipment case are endless from being completely watertight (**IP67**) to dealing with extreme temperatures from -51°C to +90°C.

Pre-Cubed foam inserts safely protect any components, sensitive equipment, and documents within the indestructible military grade equipment case.

General Specifications

Material	Polypropylene
Internal Length	See details below
Internal Width	See details below
Internal Height	See details below
Internal Dimensions	See details below
External Dimensions	See details below
Foam	Yes
Watertight or Waterproof	Yes
Wheels	No
Material Type	Plastic
Colour	See details below
Dividers	No
IP Rating	IP67
Weight	See details below

Stock No.	Brand	Product Name	Internal Dimensions (L x W x H mm)	External Dimension (L x W x H mm)	Colour	Weight (Kg)
XXX-XXXX 0707784,0707785,707785P	RS PRO	Waterproof Case	212 x 140 x 47	230 x 175 x 53	Black	0.26
XXX-XXXX 0707776,0707777,707777P	RS PRO	Waterproof Case	380 x 270 x 160	414 x 345 x 174	Black	2.45
XXX-XXXX 0707778,0707779,707779P	RS PRO	Waterproof Case	400 x 230 x 260	456 x 290 x 318	Black	2.84
XXX-XXXX 0707780	RS PRO	Waterproof Case	465 x 335 x 220	502 x 415 x 246	Black	3.96

XXX-XXXX 0707781	RS PRO	Waterproof Case	500 x 350 x 280	555 x 428 x 306	Black	5.60
XXX-XXXX 0707782	RS PRO	Waterproof Case	800 x 370 x 140	850 x 440 x 158	Black	5.74

Approvals

Declarations

REACH DoC

Similar Products

Stock No.	Brand	Product Name	Internal Dimensions (L x W x H mm)	External Dimension (L x W x H mm)	Colour	IP Rating
XXX-XXXX 0707755,0707756,0707756P	RS PRO	Waterproof Case	235 x 180 x 105	258 x 243 x 117.5	Black	IP67
XXX-XXXX 0707757,0707758,0707758P	RS PRO	Waterproof Case	235 x 180 x 156	258 x 243 x 167.5	Black	IP67
XXX-XXXX 0707761,0707762,0707762P	RS PRO	Waterproof Case	157 x 82 x 41	175 x 115 x 47	Black	IP67
XXX-XXXX 0707763,0707764,0707764P	RS PRO	Waterproof Case	157 x 82 x 41	175 x 115 x 47	Black	IP67
XXX-XXXX 0707765,0707766,0707766P	RS PRO	Waterproof Case	212 x 140x 47	230 x 175 x 53	Black	IP67
XXX-XXXX 0707768,0707769,0707769P	RS PRO	Waterproof Case	316 x 195 x 53	350 x 230 x 59	Black	IP67
XXX-XXXX 0707770,0707771,0707771P	RS PRO	Waterproof Case	316 x 195 x 81	350 x 230 x 86	Black	IP67
XXX-XXXX 0707759,0707760,0707760P	RS PRO	Waterproof Case	426 x 290 x 159	464 X 366 X 176	Black	IP67
XXX-XXXX 0707772,0707774,0707774P	RS PRO	Watertight Case	380 x 270 x 115	414 x 345 x 129	Black	IP67
XXX-XXXX 0707775	RS PRO	Watertight Case	465 x 335 x 125	502x 415 x 141	Black	IP67
XXX-XXXX 0707776,0707777,0707777P	RS PRO	Watertight Case	380 x 270 x 160	414 x 345 x 174	Black	IP67
XXX-XXXX 0707778,0707779,0707779P	RS PRO	Watertight Case	400 x 230 x 260	456 x 290 x 318	Black	IP67
XXX-XXXX 0707780	RS PRO	Watertight Case	465 x 335 x 220	502 x 415 x 246	Black	IP67
XXX-XXXX 0707781	RS PRO	Watertight Case	500 x 350 x 280	555 x 428 x 306	Black	IP67
XXX-XXXX 0707782	RS PRO	Watertight Case	800 x 370 x 140	850 x 440 x 158	Black	IP67
XXX-XXXX 0707783	RS PRO	Watertight Case	750 x 480 x 400	816 x 540 x 426	Black	IP67
XXX-XXXX 0707784,0707785,0707785P	RS PRO	Watertight Case	212 x 140 x 47	230 x 175 x 53	Black	IP67
XXX-XXXX 0707786,0707787,0707787P	RS PRO	Watertight Case	258 x 243 x 118	366 x 464 x 176	Orange	IP67
XXX-XXXX 0707788,0707790,0707790P	RS PRO	Watertight Case	258 x 243 x 168	366 x 464 x 176	Orange	IP67

XXX-XXXX 0707791,0707792,0707792P	RS PRO	Watertight Case	336 x 300 x 148	366 x 464 x 176	Orange	IP67
XXX-XXXX 0707793,0707794,0707794P	RS PRO	Watertight Case	336 x 300 x 148	366 x 464 x 176	Brown	IP67
Stock No.	Brand	Product Name	Internal Dimensions (L x W x H mm)	External Dimension (L x W x H mm)	Colour	IP Rating
XXX-XXXX 0707796,0707797,0707797P	RS PRO	Watertight Case	426 x 290 x 159	464 x 366 x 176	Orange	IP67
XXX-XXXX 0707798,0707799,0707799P	RS PRO	Watertight Case	426 x 290 x 159	464 x 366 x 176	Brown	IP67
XXX-XXXX 0707800	RS PRO	Watertight Case	500 x 350 x 211	555 x 428 x 211	Orange	IP67
XXX-XXXX 0707803	RS PRO	Roller Watertight Case	500 x 350 x 280	555 x 428 x 326	Black	IP67
XXX-XXXX 0707804	RS PRO	Roller Watertight Case	620 x 460 x 250	687 x 528 x 276	Black	IP67
XXX-XXXX 0707805	RS PRO	Roller Watertight Case	620 x 460 x 340	687 x 528 x 376	Black	IP67
XXX-XXXX 0707801	RS PRO	Roller Watertight Case	538 x 405 x 245	604 x 473 x 283	Black	IP67
XXX-XXXX 0707823,0707825,0707825P	RS PRO	Packaging Case	415 x 280 x 125	465 x 355 x 145	Black	IP65
XXX-XXXX 0707826,0707827,0707827P	RS PRO	Packaging Case	415 x 280 x 190	465 x 355 x 210	Black	IP65
XXX-XXXX 0707828,0707829,0707829P	RS PRO	Packaging Case	520 x 350 x 125	572 x 425 x 144	Black	IP65
XXX-XXXX 0707837,0707838,0707838P	RS PRO	Packaging Case	385 x 235 x 98	395 x 300 x 103	Black	N/A
XXX-XXXX 0707839,0707840,0707840P	RS PRO	Packaging Case	248 x 160 x 39	260 x 210 x 44	Black	N/A
XXX-XXXX 0707841,0707842,0707842P	RS PRO	Packaging Case	363 x 244 x 115	370 x 307 x 121	Black	N/A
XXX-XXXX 0707843,0707844,0707844P	RS PRO	Packaging Case	272 x 190 x 73	280 x 240 x 76	Black	N/A
XXX-XXXX 0707831,0707832,0707832P	RS PRO	Transit Case	324 x 252 x 87	340 x 298 x 96	Black	N/A
XXX-XXXX 0707833,0707834,0707834P	RS PRO	Tool Case	N/A	420 x 303 x 400	Blue/White	N/A
XXX-XXXX 0707835,0707836,0707836P	RS PRO	Tool Case	N/A	420 x 303 x 400	Blue/White	N/A
XXX-XXXX 0707806,0707807,0707807P	RS PRO	Assortment Box	157 x 82 x 41	175 x 115 x 47	Transparent	IP67
XXX-XXXX 0707808,0707809,0707809P	RS PRO	Assortment Box	212 x 140 x 47	230 x 175 x 53	Transparent	IP67
XXX-XXXX 0707810,0707811,0707811P	RS PRO	Assortment Box	316 x 230 x 53	350x 230 x 59	Transparent	IP67
XXX-XXXX 0707821,0707822,0707822P	RS PRO	Assortment Box	315 x 240 x 46	325 x 255 x 56	Transparent	N/A
XXX-XXXX 0707812,0707813,0707813P	RS PRO	Assortment Box, 6 compartments	155 x 98 x 31H	166 x 105 x 31H	Transparent	N/A
XXX-XXXX 0707814,0707815,0707815P	RS PRO	Assortment Box, 10 compartments	155 x 98 x 31H	166 x 105 x 31H	Transparent	N/A
XXX-XXXX 0707816,0707817,0707817P	RS PRO	Assortment Box, 13 compartments	155 x 98 x 31H	166 x 105 x 31H	Transparent	N/A

xxx-xxxx 0707819,0707820,707820P	RS PRO	Assortment Box, 15 compartments	155 x 98 x 31H	166 x 105 x 31H	Transparent	N/A
-------------------------------------	--------	------------------------------------	----------------	-----------------	-------------	-----

Stock No. xxx-xxx
MAX002VGPB

IP67



- External dimension 230 x 175 x 53H mm
- Internal dimension 212 x 140 x 47H mm
- Weight: 0.26kg
- Temperature rating: -10 to 80°C
- Capacity: Capacity: 1.39 lt

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins corrosion free
- Foam

Stock No. xxx-xxx
MAX380H160S

A foldable pull-out handle

IP67



- External dimension 414 x 345 x 174H mm
- Internal dimension 380 x 270 x 160H mm
- Weight: 2.45kg
- Temperature rating: -51 to 90°C
- Capacity: Capacity: 16.41 lt

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins corrosion free
- Pre-cut cubed foam
-

Stock No. xxx-xxx
MAX400S

A foldable pull-out handle

IP67



- External dimension 456 x 290 x 318H mm
- Internal dimension 400 x 230 x 260H mm
- Weight: 2.84kg
- Temperature rating: -51 to 90°C
- Capacity: 22 lt

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins corrosion free
- Pre-cut cubed foam

Stock No. xxx-xxx
MAX465H220S

A foldable pull-out handle

IP67



- External dimension 502 x 415 x 246H mm
- Internal dimension 465 x 335 x 220H mm
- Weight: 3.96kg
- Temperature rating: -51 to 90°C
- Capacity: 34.27 lt

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins corrosion free
- Pre-cut cubed foam

Stock No. xxx-xxx
MAX505H280S

A foldable pull-out handle

IP67



- External dimension 555 x 428 x 306H mm
- Internal dimension 500 x 350 x 280H mm
- Weight: 5.60kg
- Temperature rating: -51 to 90°C
- Capacity: 49 lt

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins corrosion free
- Pre-cut cubed foam

Stock No. xxx-xxx
MAX800S

A foldable pull-out handle

IP67



- External dimension 850 x 440 x 158H mm
- Internal dimension 800 x 370 x 140H mm
- Weight: 5.74kg
- Temperature rating: -51 to 90°C
- Capacity: 41.44 lt

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins corrosion free
- Pre-cut cubed foam