



Product data sheet

Power tools for trade & industry

Wet/Dry Extractor

GAS 35 H AFC



H-Class versatile wet/dry dust extractor with automatic filter cleaning developed for hazardous dust

The most important data

Weight	12.4 kg
Container volume, net	23 l
Filter surface area	5,000 cm ²

Part Number 0 601 9C3 660

[> More product information](#)

Technical data

Technical data

Rated input power	1,200 W
Weight	12.4 kg
Container volume, gross	35 l
Container volume, net	23 l
Container volume, net, water	19.2 l
Dust class of wet/dry extractor	H
Dust class	H
Tool dimensions (width)	375 mm
Tool dimensions (length)	515 mm
Tool dimensions (height)	575 mm
Filter surface area	5,000 cm ²
Max. airflow rate (turbine)	74 l/s
Max. vacuum pressure (turbine)	254 mbar
Wheels, number	4



Product data sheet

Power tools for trade & industry

Advantages:

- H-class certified for carcinogenic and pathogenic dust, increasing user protection
- Automatic filter cleaning mechanism for constant working
- Flow control monitoring constant air flow through the suction cup, including an acoustic warning signal

