

IS-3 Standard ; 0 ... 60 bar; 4...20 mA, 2-wire

IS-3 Standard ; 0 ... 60 bar; 4...20 mA, 2-wire

Item number: 14122703

Quantity: 1 pcs.

Order code: IS-3-0-2211-1ZZ-BBNHSZZ-GTA3ZZZ-UAZZ
6W101AIS3ZZSF2ASQOGSI3

Overview: IS-3 Standard ; 0 ... 60 bar; 4...20 mA, 2-wire
@ 10 ... 30 V DC
Accuracy: 0.5% of span
G 1/2 B EN 837
Sealing: without
Wetted parts: stainless steel
Adjustability: Zero/span adjustable
angular connector acc. to DIN EN 175301-803 A PG9
Cable material: without
Cable length: without
U+=1, U-=2
permitted media temperature: -20...+80°C
Approvals: ATEX/IECEX
II 1/2G Ex ia IIC T4/T5/T6 Ga/Gb, I M1 Ex ia I Ma
Additional certifications: without
Special features: without
Test protocol: without test protocol
Additional ordering information: without
Specifications according to data sheet: PE 81.58

Details: IS-3 Standard ; 0 ... 60 bar; 4...20 mA, 2-wire
@ 10 ... 30 V DC
Accuracy: 0.5% of span
G 1/2 B EN 837
Sealing: without
Wetted parts: stainless steel
Adjustability: Zero/span adjustable
angular connector acc. to DIN EN 175301-803 A PG9
Cable material: without
Cable length: without
U+=1, U-=2
permitted media temperature: -20...+80°C
Approvals: ATEX/IECEX
II 1/2G Ex ia IIC T4/T5/T6 Ga/Gb, I M1 Ex ia I Ma
Additional certifications: without
Special features: without
Test protocol: without test protocol
Additional ordering information: without

Date: 23/01/2024



Specifications according to data sheet: PE 81.58