



Fingertip

Natural rubber doormat gives dirt the brush-off

- Flexible natural rubber nodules deliver excellent dirt scraping and trapping action.
- Dirt is effectively brushed off then retained in a solid base.
- Ideal for all weather conditions making it suitable for outdoor use.
- Slip-resistant base to help retain position.
- Safety bevelled edges all round.

Product height: 16mm

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.35 x 0.6m x 10mm	1.25	17.5 x 17.5 x 105	Box		1	Black	FT010007
0.6 x 0.8	5	17.5 x 17.5 x 75	Box		1	Black	FT010001
0.8 x 1	9	17.5 x 17.5 x 105	Box		1	Black	FT010002
0.9 x 1.8	15	23 x 23 x 124	Box		1	Black	FT010003

Surface Material:	Natural rubber
Surface Finish:	Moulded flexible fingers
Product Height:	16mm nominal
Operating Temperature:	-20° - + 160° C
Resistance to Chemicals:	N/A
Environmental Resistance:	Ideal for indoor and outdoor applications.
UV Resistance:	Yes
Typical Applications:	Entrance areas.
Installation Method:	Loose lay
Cleaning Method:	Wet/Dry vacuum or simply wash down with hose.

Product Performance:

Fatigue:	N/A
Slip Resistance:	● ● ●
Wear:	● ● ●
Low ‡ High	● → ● ● ● ● ●

Flame Retardancy:	N/A
Country of Origin:	Sri Lanka

End of document

United Kingdom

COBA Europe Ltd
Marlborough Drive
Fleckney, Leicestershire
LE8 8UR

+44 (0)116 240 1088
sales@cobaeeurope.com
www.cobaeeurope.com

Germany

COBA Europe GmbH
Pullenweg 1 - 3
41352 Korschenbroich

+49 (2161) 2945-0
verkauf@cobaeeurope.de
www.cobaeeurope.de

Slovakia

COBA Europe s.r.o.
Terchová - Vyšné Kamenec 11
SK-013 06

+421 41 507 11 12
sales@cobaeeurope.sk
www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.