



Fuse-link, medium voltage, 10 A, AC 17.5 kV, 35.5 kA, 2", 51 x 292 mm, back-up, DIN, with striker



Part no. 17.5KV 10AMP 2" DIN FUSE
Catalog No. 17.5DLSJ10

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			medium voltage
Rated current	I	A	10
Rated voltage			AC 17.5 kV
Construction size			2"
Size			51 x 292 mm
Utilization category			back-up
Status indicator			with striker
Breaking Capacity		kA	35.5
usable for size/applications			transformer protection indoor use
Standard/Approval			DIN
Standards/Regulations			DIN 43625 VDE 0670-4 VDE 0670-402 IEC 60282-1

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Medium-/high voltage fuse (EC003507)			
Rated current		A	10
Rated voltage		kV	17.5
Voltage type			AC
Rated frequency		Hz	50 - 50
Breaking capacity		kA	35.5
Utilization category			Other
Application			Primary side transformer protection
Length		mm	292
Diameter		mm	51
Performance category according to IEC 60282-1			Back-up
With striker			Yes
Standard			DIN
Release characteristic			Other
Installation technique			Air