

## Features

- Specifically designed for locking and securing ball valves in various positions (open or closed) across different sizes and types of valves.
- Constructed from super-tough nylon and stainless steel, providing resistance to corrosion and durability in various environmental conditions.
- Ideal for use in gaseous, oil, liquid, and air pressure pipes and valves, providing a wide range of industrial applications.
- Allows valves to be locked in ON or fixed positions for non-lockout applications, enhancing operational flexibility.

## RS PRO Settable Ball Valve Lockout-Small

RS Stock No.: 0276135



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

- *Used for precisely locking & closing/opening ball valves of various sizes and makes.*
- *Constructed from super tough nylon and stainless steel to avoid corrosion. Designed to lock out quarter-turn valves of varying sizes and geometric handle dimensions (round, square or flat) up to 1 - 1/4" thick x 1-5/8" wide and various lengths. Valves can also be locked in the ON or fixed positions for non-lockout applications. To freeze the valve handle at an exact location, attach the second arm (sold separately) to the lock handle of 2 / 3 / 4, or 5-way valves.*
- *Ideal for all kinds of usage areas/pipelines like gaseous, oils, liquids, air pressure pipes & valves etc.*

## General Specifications

Type	Ball Valve Lockout
Material	Nylon & Stainless steel
Colour	Red

## Mechanical Specifications

Length	182mm
Width	53mm
Height	290mm
Weight	472 Grams

## Operation Environment Specifications

Withstand temperature	-20°C to 120°C (-4°F to 248°F)
-----------------------	--------------------------------