

Features

- Draughting medium back chair including ring kit conversion
- Wipe clean finish
- Backrest with height adjustment and hinged tilt
- Tamper proof seat fixings
- Generous seat size
- Gas lift seat height adjustment
- Footring for 'off floor' support
- Height adjustable footring and extended gas lift
- Durable nylon base with glides for stability
- Accepts optional fixed or adjustable armrests
- Requires easy self-assembly
- Available from stock in black, white and Blue PU

RS PRO Office Chairs

RS Stock No.: 0625812



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This Office Ergo Blaster Black PU Standard Drafter chair is our entry level solution for counter work, easy to use and with a fixed footring for "off floor" support. It has a medium sized backrest with height adjustment, tamper proof seat fixings, a height adjustable wipe clean seat and fixed glides to stop the chair rolling away!

General Specifications

Features	Draughting medium back chair including ring kit conversion, Backrest with height adjustment and hinged tilt, Wipe clean finish, Generous seat size, Gas lift seat height adjustment, Footring for 'off floor' support, Deluxe version offers a height adjustable footring and extended gas lift, Durable nylon base with glides for stability
Chair Type	Draughter
Seat Material	PU
Weight Capacity	90kg
Seat Height	60-86 cm
Colour	Black