

3240926

https://www.phoenixcontact.com/gb/products/3240926

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable gland, metric thread, IP66 protection, angled



### Commercial data

Item number	3240926
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AF7DSA
Product key	AF7DSA
Catalog page	Page 589 (C-3-2019)
GTIN	4046356710336
Weight per piece (including packing)	10.8 g
Weight per piece (excluding packing)	10.8 g
Customs tariff number	39174000
Country of origin	DE



3240926

https://www.phoenixcontact.com/gb/products/3240926

### Technical data

### Product properties

Product type	Protective hose screw connection
Application	Cable gland
Type of the screw connection	Conduit adapter
Туре	Outer thread
Cable outlet	angled
Thread type	metric

### Dimensions

Width	23 mm
Height	42 mm
Length	41.5 mm
Diameter	24.5 mm

### Material specifications

Material	PA 6
Flammability rating according to UL 94	V2
Material for screw connection	PA
Components	free from silicone, halogen, and cadmium

### Cable/line

Halogen-free	yes

### Mechanical properties

#### Mechanical data

Type of the screw connection	Conduit adapter
Type of the solew confidence	Conduit adapter

#### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C 120 °C



3240926

https://www.phoenixcontact.com/gb/products/3240926

### **Approvals**

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/3240926



UL Recognized
Approval ID: E86359



LR



VDE approval of drawings



3240926

https://www.phoenixcontact.com/gb/products/3240926

### Classifications

EC	LASS

ECLASS-13.0 27430311	
ETIM	
ETIM 9.0 EC001178	
UNSPSC	
UNSPSC 21.0 39121300	



3240926

https://www.phoenixcontact.com/gb/products/3240926

### Environmental product compliance

#### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT Ltd Halesfield 13, Telford Shropshire, TF7 4PG 01952 681700 info@phoenixcontact.co.uk