



COBAdot Vinyl Versatile PVC floor covering

- Resilient PVC flooring with smart studded surface.
- A practical solution for refurbishing floors.
- Effectively helps to insulate buildings with cold concrete floors.
- Beneficial in reducing noise levels.
- Can be loose laid or bonded to the floor surface.
- Contains 10% rubber content for tear-resistance.



Technical Specification

Material:	PVC
Surface Finish:	Studded
Product Height:	2.5mm
Operating Temperature:	-5°C to 60°C
Typical Applications:	A practical solution for refurbishing floors
Installation Method:	Loose laid or bonded to the floor surface
Country of Origin:	China

Sizes	Black	Weight
1.2m x 10m	CDS010001V	31.30 kg
1.2m x per linear metre	CDS010001VC	4.50 kg