

LONG LASTING SPRAY GREASE




PRODUCT OVERVIEW

A premium quality spray grease designed for use in areas where long-term lubrication and corrosion protection is required. It is particularly suitable for use on vertical surfaces, where its viscous nature prevents running and displacement. The back-bone of the formula is WD-40® itself, ensuring an excellent performance profile.

FEATURES AND BENEFITS

- ⊕ Non-drip formula - stays where it's applied, doesn't run
- ⊕ Very long lasting and economical, contains WD-40® MUP
- ⊕ Precise application thanks to Smart Straw
- ⊕ Excellent lubrication and water-displacement properties
- ⊕ Excellent corrosion protection
- ⊕ Excellent adhesion and sealing properties
- ⊕ High degree of water resistance
- ⊕ Excellent load carry capacity and good oxidation resistance
- ⊕ Wide temperature range of -20°C to +115°C as grease, then to +260°C as liquid



TYPICAL APPLICATIONS

Virtually limitless application areas throughout the home, trade and industry. Any metallic surfaces requiring lubrication and corrosion protection. This product will also protect against seizure caused by corrosion and chemical attack.

DIRECTIONS FOR USE

Spray sparingly onto the component, ensuring an even coating.

TECHNICAL DATA

PROPERTY	LONG LASTING SPRAY GREASE
Appearance	An amber aerosol grease, with the characteristic WD-40® aroma
4-ball Wear Test	0.5mm (ASTM D-4172)
Dropping Point Temperature	118°C (ASTM D566)
Corrosion Protection in salt spray test	0% rust at 72h (ASTM B-117)
Flammability	Extremely flammable
Temperature (Continuous)	-20°C to +115°C as grease, then to +260°C as liquid

PACKAGING SPECIFICATIONS

PRODUCT NUMBER	UNIT SIZE	CASE SIZE
44217	400ml	400ml x 12

This information is provided in good faith based upon data and sources believed to be reliable and correct. Conditions of use, outside the control of the Company, dictate that no responsibility can be assumed for the ultimate performance of this product.

