



#### Main

|                             |                                                            |
|-----------------------------|------------------------------------------------------------|
| Range of product            | 9007                                                       |
| Series name                 | Miniature potted                                           |
| Product or component type   | Limit switch lever                                         |
| Device short name           | 9007MS/ML                                                  |
| Associated complete product | 9007MS04..<br>9007ML04..                                   |
| Movement of operating head  | Rotary                                                     |
| Type of operator            | Cast zinc spring return roller lever length: 50.80 mm -    |
| Type of roller              | 1 nylon inside roller diameter: 19.05 mm - width: 25.40 mm |
| Type of approach            | Lateral approach                                           |
| Positive opening            | Without                                                    |

#### Complementary

|                  |            |
|------------------|------------|
| Tracks           | 0.875 in   |
| Switch actuation | By 30° cam |
| Net weight       | 0.05 kg    |

#### Environment

|                                       |                      |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -40...221 °F         |
| Ambient air temperature for storage   | -40...221 °F         |
| Environmental characteristic          | Standard environment |

#### Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 6.452 cm  |
| Package 1 Width              | 2.54 cm   |
| Package 1 Length             | 16.387 cm |
| Package 1 Weight             | 45.359 g  |

#### Offer Sustainability

|                                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|--------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65                  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| For all Reach Rohs enquiries contact us at | <a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>                                                                                                                                                                                                                                                                                                    |

#### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|