



Product designation
Product type designation

Description

Accessories for

Shunt trip
P5X16A400UL
Shunt trip
releases for UL
certified MCCBs.
Accessories for
UL-compliant
MCCBs

Operational characteristics

Rated supply voltage AC	VAC	380...500
Rated frequency	Hz	45...65
In-rush consumption	VA	1.15
Operating voltage	US	70...110
Average opening time	ms	50

Mechanical features

Tightening torque for terminals	min	Nm	0.8
	max	Nm	1
	min	lbin	7
	max	lbin	9

Conductor section	AWG/Kcmil	min	20
		max	16
Flexible w/o lug conductor section	min	mm ²	0.5
	max	mm ²	1.5
Flexible c/w lug conductor section	min	mm ²	0.5
	max	mm ²	1.5

Terminals	type	Screw
	tool	PZ2
Weight	g	50



Wiring diagrams

Certifications and compliance

Certificates

cULus

ETIM classification

EC000066 - Power contactor, AC switching