

Actuator

45-
2N42.2010.000

Distribution by
Rs-online



<https://rs-online.eao.com/p/45-2N42.2010.000>

Your product:



45-2N42.2010.000

Actuator

FRONT

Front dimension:	Ø 29,5 mm
Front form:	Round
Front bezel colour:	Silver
Front bezel material:	Metal

MOUNTING

Design:	Raised
Mounting cut-out:	Ø 22.3 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lever colour:	Black
Lever material:	plastic

MECHANICAL CHARACTERISTIC

Switching action:	Maintained
Mechanical lifetime:	1 Mil. cycles of operation
Operating frequency:	1 800/h
Weight:	0.038 kg

AMBIENT CONDITION

IP front protection:	IP66, IP67, IP69K
----------------------	-------------------


Operating temperature:	– 25 °C ... + 70 °C
Storage temperature:	– 40 °C ... + 80 °C
Shock resistance:	According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms
Vibration resistance:	According to IEC 60068-2-6: 10 ... 500 Hz: 5 g
Climate resistance:	During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6

CERTIFICATE


REACH:	REACH compliant
RoHS:	RoHS compliant

OTHER

Short Description:	Actuator, Ø 22.3 mm, Ø 29,5 mm, Black, Round, Silver, Metal, Maintained, IP66, IP67, IP69K
Housing material:	Metal
Hints:	Reset from above
Wiring diagrams:	



Mounting cut-outs:



Dimension drawings:

